

ROICA Contour™ family is a unique family of premium stretch yarns for a more durable and calibrated shape control. Choosing fabrics for garments with ROICA Contour™ family INSIDE creates confidence and security through its fit, focused compression for shaping and muscle support performance exactly where it is needed.

ROICA™ SF

Application | ACTIVATION / AQUA / STYLE#FIT / LEGWEAR / ESSENTIALS



SHAPE CONTROL



CALIBRATED FIT



COMFORT




ADVANCED STRETCH

A stretch yarn that provides better adhesion, keeping fabrics flatter, with no-fray raw-cut edges for stylish designs and smooth comfort in wear.

- Run resistance
- Curl resistance and fray resistance, for stylish designs and smooth comfort in wear

▼ Yarns lock to each other due to the heat generated during processing



Yarns get tangled tightly and become hard to separate from each other



Yarn surface of an adhesive point

▼ Run resistance:

Even if a hole occurs, it resists running

Comparison using a pantyhose

ROICA™ SF




Basic ROICA™




▼ Curl resistance

ROICA™ SF



Basic ROICA™



< Sample > Circular-knit jersey fabric

Ny 33dt/26f x ROICA™ SF 33dt


Ny 33dt/26f x Basic ROICA™ 33dt

< Test method >


Wash 15 min with 1:30 fabric/water ratio then rinse 5 min: all at 40°C.

▼ Fray resistance

ROICA™ SF



Basic ROICA™



< Sample > Rachel circular-knit fabric

Ny 44dt/34f x ROICA™ SF 44dt and 155dt

Ny 44dt/34f x Basic ROICA™ 44dt and 155dt

< Test method >

Wash 15 min with 1:30 fabric/water ratio 50 times, then rinse 5 min: all at 40°C.